

Fiche technique

Mélange / Agitateurs magnétiques



RO 10

10-position digital magnetic stirrer without heating, designed for synchronous stirring. The magnetic coil technology provides noiseless and consistent stirring on all positions. Speed remains constant, even when load changes. The closed and compact design allows easy cleaning and protects the equipment against the penetration of liquids. Additionally, a removable transparent anti-slip mat is included.

- Adjustable reverse operation
- Wear free magnetic coils
- Error code display
- Easy operation with touch keypad
- Suitable for continuous operation
- Adjustable speed in increments of 10 rpm

Accessoires: IKAFLON® 10 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 15 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® glass 25 Set (5 Pcs) round Magnetic stirring bars, IKAFLON® glass 30 Set (5 Pcs) round Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) power SmSo PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) power SmSo PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) slide round

Données techniques

Nombre de postes	10
Espaces entre les postes [mm]	90
Plage de vitesse de chaque poste [%]	0
Capacité d'agitation max. (H ₂ O) [l]	0.4
Possibilité de réglage de la vitesse	10 échelle RPM
Plage de vitesse [rpm]	0 - 1200
longueur min. du barreau aimanté [mm]	25
Dim. max. des barreaux aimantés [mm]	30
Matériaux de la plaque	Inox 1.4301
Dimensions de la plaque [mm]	190 x 470
Dimensions (L x P x H) [mm]	190 x 60 x 570
Poids [kg]	5
Plage de température du milieu admise [°C]	5 - 40
Humidité relative admissible [%]	80
Protection selon DIN EN 60529	IP 40
Tension [V]	100 - 240
Fréquence [Hz]	50/60
Puissance absorbée de l'appareil [W]	25
Tension continue [V=]	24
Consommation électrique max. [mA]	1000

Ident. N°. 0003691000

PTFE-coated Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 10 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 9 Set (5 Pcs) crown PTFE-coated Magnetic stirring bars, TRIKA® 25 Set (5 Pcs) PTFE-coated Magnetic stirring bars, H 11 Cordon d'alimentation, H 11 Cordon d'alimentation CH-Connecteur, RSE Extracteur de barreaux, BC 1000 Couvercle pour bécher, H 11 Cordon d'alimentation UK-Connecteur, H 11 Cordon d'alimentation USA-Connecteur

DOMINIQUE DUTSCHER SAS