



## S 50 N - W 80 SMK Jet mixer head

Suitable for dispersing instrument T 50 digital

For shortening mixing and dissolving times. The vertical flow and the high circumferential speed up to 10.000 rpm ensure intensive mixing. The head is used for adding gases or liquids, for lumpfree suspension of difficult to dissolve powders or for dissolving sedimented, already hardened substances.

Immersion depth: 140 - 350 mm

Working range: 1 - 50 l

Generator diameter: 80 mm

Materials in contact with medium: PTFE, AISI 316L

Suitable for solvents: yes

Max. temperature: 180 °C

Sterilization methods: all methods