

Data Sheet

Mixing / Magnetic Stirrers



RET basic

Wide speed range from 0/50 - 1700 rpm

Integrated temperature control

Incl. PT 1000 temperature sensor (PT 1000.60)

Exact temperature and speed setting via digital display, even when switched off

Set safety temperature limit displayed digitally

Hot Top indicator >> hot surface warning to prevent burns!

Digital error code display

- With adjustable safety circuit of heating plate temperature (50 - 380 °C)
- Safety magnetic stirrer with heating, suitable for unsupervised operation
- Bushing according to DIN 12878 for connecting a contact thermometer, e.g. ETS-D5, enables precise temperature control
- High level of safety thanks to improved heat control technology
- Enclosed assembly (IP 42) guarantees long service life
- Very broad temperature range (RT - 340 °C)
- Extremely fast heating times
- Electronic speed control
- High magnetic adhesion
- Incl. protection cover H 100

Accessories: ETS-D5, ETS-D6, PT 1000.60 Temperature sensor, stainless steel, PT 1000.70 Temperature sensor, glass coated, PT 1000.80 Temperature sensor, stainless steel, PT 1000.90 Temperature sensor, coated, RS 1 Set of magnetic stirring bars, IKAFLON® 10 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 15 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 40 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 50 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 80 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® glass 25 Set (5 Pcs) round Magnetic stirring bars, IKAFLON® glass 30 Set (5 Pcs) round Magnetic stirring bars, IKAFLON® glass 40 Set (5 Pcs) round Magnetic stirring bars, IKAFLON® glass 50 Set (5 Pcs) round Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) power SmSo PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) power SmSo PTFE-coated Magnetic stirring bars, IKAFLON® 50 Set (5 Pcs) power SmSo PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 40 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 50 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 35 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 40 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 50 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 60 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 70 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 10 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 38 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 37 Set (5 Pcs) bone PTFE-coated Magnetic stirring bars, IKAFLON® 54 Set (5 Pcs) bone PTFE-coated Magnetic stirring bars, IKAFLON® 67 (1 Pc) beaker PTFE-coated Magnetic stirring bars, IKAFLON® 74 (1 Pc) beaker PTFE-coated Magnetic stirring bars, IKAFLON® 103 (1 Pc) beaker PTFE-coated Magnetic stirring bars, IKAFLON® 125 (1 Pc) beaker PTFE-coated Magnetic stirring bars, IKAFLON® 9 Set (5 Pcs) crown PTFE-coated Magnetic stirring bars, RS 2 Set of magnetic stirring bars, TRIKA® 25 Set (5 Pcs) PTFE-coated Magnetic stirring bars, TRIKA® 35 Set (5 Pcs) PTFE-coated Magnetic stirring bars, TRIKA® 55 Set (5 Pcs) PTFE-coated Magnetic stirring bars, TRIKA® 80 Set (5 Pcs) PTFE-coated Magnetic stirring bars, RSE Stirring bar remover, H 135.10 Square carrier without handle, H 135.11 Square carrier with handle, H 135.101 Block 16 x 4 ml, H 135.102 Block 16 x 8 ml, H 135.103 Block 9 x 16 ml, H 135.104 Block 4 x 20 ml, H 135.105 Block 4 x 30 ml, H 135.106 Block 4 x 40 ml, H 135.107 Block 100 ml, H 135.108 Block

250 ml, H 135.20 Flask carrier 100 ml without handle, H 135.21 Flask carrier 100 ml with handle, H 135.201 Flask inlay 10 ml, H 135.202 Flask inlay 25 ml, H 135.203 Flask inlay 50 ml, H 135.25 Flask carrier 250 ml without handle, H 135.26 Flask carrier 250 ml with handle, H 135.30 Flask carrier 500 ml without handle, H 135.31 Flask carrier 500 ml with handle, H 135.301 Flask inlay 100 ml, H 135.302 Flask inlay 250 ml, H 135.40 Flask carrier 1000 ml without handle, H 135.41 Flask carrier 1000 ml with handle, H 135.401 Flask inlay 500 ml, H 135.50 Flask carrier 2000 ml without handle, H 135.51 Flask carrier 2000 ml with handle, H 135.501 Flask inlay 1000 ml, H 16 V Support rod, H 16.3 Extension, H 38 Holding rod, H 44 Boss head clamp, H 100 Protective cover, H 29 Oil bath attachment, H 30 Oil bath attachment, labworldsoft®, H 11 Mains cable Euro plug, H 11 Mains cable CH plug, H 11 Mains cable UK plug, H 11 Mains cable USA plug, LABLIFT m, BC 1000 Beaker cap, HG 600 Heating jacket, HG 1000 Heating jacket

Technical Data	
Number of stirring positions	1
Stirring quantity max. per stirring position (H ₂ O) [l]	20
Motor rating output [W]	9
Direction of rotation	right
Speed display set-value	LED
Speed display actual-value	LED
Speed control	Turning knob
Speed range [rpm]	50 - 1700
Setting accuracy speed [rpm]	1
Stirring bar length min. [mm]	20
Stirring bar length max. [mm]	80
Self-heating of the hotplate by max. stirring (RT:22°C/duration:1h) [+K]	15
Heat output [W]	600
Temperature display set-value	LED
Temperature display actual-value	LED
Temperature unit	°C
Heating temperature range [°C]	Room temp. + device self heating - 340
Heat control	Turning knob
Temperature setting range min. [°C]	0
Temperature setting range max. [°C]	340
Heating rate heating plate [K/min]	7
Temperature setting resolution of heating plate [K]	1
Connection for ext. temperature sensor	PT1000
Temperature setting resolution of medium [K]	1
Adjustable safety circuit min. [°C]	50
Adjustable safety circuit max. [°C]	360
Set-up plate material	stainless steel 1.4301
Set-up plate dimensions [mm]	Ø 135
Automatic reverse rotation	no
Intermittend mode	no
Viscosity trend measurement	no
Break detection stirring bar	no
Timer	no
pH measurement	no
Graph function	no
Programs	no
Sensor in medium detection (Error 5)	yes
Weighing function	no
Dimensions (W x H x D) [mm]	160 x 95 x 270
Weight [kg]	2.5
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 42
RS 232 interface	no
USB interface	no
Analog output	no
Voltage [V]	220 - 230 / 115 / 100
Frequency [Hz]	50/60
Power input [W]	630
Ident. No.	0003622000