

Data Sheet

Mixing / Overhead Stirrers



RW 28 digital

Powerful, mechanically controlled laboratory stirrer designed for highly viscous applications for quantities up to 80 l (H₂O). It is suitable for intensive mixing for use in laboratories and pilot plants. The stirrer comes equipped with a protection for overheating of the motor by means of self-locking temperature limiter. Additionally, to secure bowls, a stirring shaft protection and clamping fixture are optionally available.

- Digital speed display
- Infinitely adjustable speed from 60 to 1400 rpm in two speed ranges
- Push-through agitator shafts
- Overload protection
- Error code display
- Robust, ergonomic design
- Quiet operation
- With constant power-drive

Accessories: R 1385 Propeller stirrer, 3-bladed, R 1388 Propeller stirrer, 3-bladed, R 1300 Dissolver stirrer, R 1345 Propeller stirrer, 4-bladed, R 1375 Paddle stirrer, R 1376 Paddle stirrer, R 1355 Centrifugal stirrer, R 2722 H-Stand, R 2723 Telescopic stand, R 1331 Anchor stirrer, R 1313 Turbine stirrer, FK 1 Flexible coupling, R 1302 Dissolver stirrer, R 301 Stirring shaft protection, R 301.1 Support holder, R 271 Boss head clamp, R 1333 Anchor stirrer, RH 5 Strap clamp

Technical Data

Stirring quantity max. per stirring position (H ₂ O) [l]	80
Motor rating input [W]	220
Motor rating output [W]	90
Speed display	LED
Speed range [rpm]	60 - 1400
Viscosity max. [mPas]	50000
Output max. at stirring shaft [W]	90
Permissible ON time [%]	100
Torque max. at stirring shaft [Ncm]	900
Torque max. at stirring shaft at 60 1/min (overload) [Ncm]	1144
Torque max. at stirring shaft at 100 1/min [Ncm]	900
Torque max. at stirring shaft at 1.000 1/min [Ncm]	86
torque I max. [Ncm]	900
torque II max. [Ncm]	300
Speed range I (50 Hz) [rpm]	60 - 400
Speed range II (50 Hz) [rpm]	240 - 1400
Speed range I (60 Hz) [rpm]	72 - 480
Speed range II (60 Hz) [rpm]	288 - 1680
Speed control	stepless
Setting accuracy speed [±rpm]	1
deviation of speed measurement [±rpm]	10

Stirring element fastening	chuck
Chuck range min. diameter [mm]	1
Chuck range max. diameter [mm]	10
Hollow shaft, inner diameter [mm]	10.5
Hollow shaft (push-through - when stopped)	yes
Fastening on stand	extension arm
Extension arm diameter [mm]	16
Extension arm length [mm]	145
Torque display	no
Speed control	mechanical
Nominal torque [Nm]	9
housing material	alu-cast coating / thermoplastic polymer
clean room qualified	no
explosion proofed	no
Noise without element [dB(A)]	62.5
Dimensions (W x H x D) [mm]	123 x 364 x 252
Weight [kg]	7.5
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 40
USB interface	no
RS 232 interface	no
Analog output	no
Voltage [V]	220 - 240 / 115 / 100
Frequency [Hz]	50/60
Power input [W]	220
Ident. No.	0005040000