

### ClearLine glass microfiber filter without binder

Made with 100% borosilicated microglass fibers, these filters offer an excellent level of very small particles retention (up to 0,7  $\mu\text{m}$ ) and a large loading capacity. They are particularly suitable for micro-filtration of air, gases and liquids as they resist to 500 °C and are compatible to most solvents and reagents (except hydrofluoric acid)

Application : Water analysis

Weight DIN 53104 : 143 g/m<sup>2</sup>

Thickness : 0,70 mm

Pore size : 1  $\mu\text{m}$

Filtration speed DIN 53137 : 200 sec

Burst strength : 50 kPa

Dimensions : 42,5 mm

**Unités :**

50 filters