

ClearLine glass microfiber filter with binder

The glass microfiber filters with binder have a lower resistance to temperature (up to 180 °C maximum). The hydrophobic grade [FV27] is suitable for air and gas analysis. At the opposite, the hydrophilic grade [FV29] is adapted to liquid filtration.

Application : Air pollution and exhaust fume control

Weight DIN 53104 : 73 g/m²

Thickness : 0,40 mm

Propriété : Hydrophobic

Retention efficiency for 0,3 µm : 0,999

Retention : -

Dimensions : 70 mm

Units :
50 filters