

### ClearLine glass microfiber filter with binder

The glass microfiber filters with binder have a lower resistance to temperature (up to 180 °C maximum). The hydrophobic grade [FV27] is suitable for air and gas analysis. At the opposite, the hydrophilic grade [FV29] is adapted to liquid filtration.

Application : Gravimetric analysis

Weight DIN 53104 : 73 g/m<sup>2</sup>

Thickness : 0,35 mm

Propriété : Hydrophilic

Retention efficiency for 0,3 µm : 0

Retention : 0,6 µm

Dimensions : 90 mm

**Units :**  
**50 filters**