



---

## MQ - 250 ml

### Summary

MQ Mantles heaters were developed by FALC in compliance with the latest European Safety Standards.

### Description

MQ Mantles heaters were developed by FALC in compliance with the latest European Safety Standards.

They feature completely new characteristics and a new inclined front side ensures easy value adjustment and read – out.

Housing in steel plate, oven coated with acidproof epoxy paint, which includes heating resistances built in a fiberceramic block.

The device is fitted with an aluminium calotte covered with fiberglass cloth and with a bottom hole for fluid collection in case of matrass breaking.

A threaded M8 hole for support rod insertion is fitted on the heater back side. Heaters feature an ON / OFF switch with green light and a thermostat with fluid expansion graduated probe for temperature control, which ensures temperature accuracy.



### Features



Item	625.0540.02
Temperature	+350
External dimension (LxWxH)	mm 175x250x115
Power	V/HZ 230/50-60
Weight	Kg 2.0
Protection class	IP 41
Flask	ml 250
Precision on the plate	$\pm 2$
Heating res. capacity	W 180

DOMINIQUE DUTSCHER SAS