



LH

Overhead Stirrers

Overhead stirrer with 80 Ncm torque
for medium-high viscosity application



Resistant and Easy-to-Use

The LH is an intuitive overhead stirrer ensuring safety with overload, over-current and overheating protection.

- Maximum torque of 80 Ncm
- Supports applications with a maximum viscosity of 50 000 mPa*s
- Electronic speed regulation from 50 to 2000 rpm, up to 40 L
- Long life, robust motor
- Easy-chuck to change the shafts without tools
- Automatically stops if blocked – no burn-out or damage
- Overload, overcurrent and overtemperature protection
- Sealed to IP 40 standard



INSTRUMENT - CODE

LH

110-230 V / 50-60 Hz

F201A0156

TECHNICAL DATA

CONSTRUCTION MATERIAL	Technopolymer and epoxy painted aluminum alloy
CHUCK RANGE	1 - 10 mm
ELECTRONIC PROTECTION RATING CEI EN 60529	IP 40
ELECTRONIC SPEED REGULATION	From 50 to 2000 rpm
STIRRING VOLUME MAX (H ₂ O)	Up to 40 L
MAX VISCOSITY	50000 (mPa*s)*
TORQUE MAX	80 Ncm
ALLOWED ROOM TEMPERATURE	From 0 to 40 °C
DIMENSION (WXHxD)	80x230x196 mm
POWER	190 W
WEIGHT	2.9 Kg



We reserve the right to make technical alterations
We do not assume liability for errors in printing, typing or transmission

VELP Official Partner

DESIGNED AND MANUFACTURED IN ITALY



ITALY - HQ
Via Stazione 16
20865 Usmate (MB) Italy
Tel. +39 039 628811
velpitalia@velp.com

INDIA
velpindia@velp.com

USA
155 Keyland Court, Bohemia
NY 11716 - U.S.
Tel. +1 631 573 6002
velpusa@velp.com

CHINA
Xinlong Rd Building 28, Lane 1333
Shanghai city - China
Tel. +86 180 1755 7329
velpchina@velp.com