

Brand: Honeywell Fluka
 Product: 30721

Hydrochloric acid puriss. p.a., ACS reagent, reag. ISO, reag. Ph. Eur., fuming, 37%, APHA: 10

Parameter	Specification	Units
assay	37-38.0	%
density (20°C)	min. 1.18	g/ml
residue on ignition (SO ₄)	max. 5	ppm
non-volatile matter	max. 0.005	%
ammonium (NH ₄)	max. 1	ppm
silver (Ag)	max. 0.01	ppm
aluminium (Al)	max. 0.000005	%
arsenic (As)	max. 0.01	ppm
barium (Ba)	max. 0.000002	%
beryllium (Be)	max. 0.000002	%
bismuth (Bi)	max. 0.1	ppm
calcium (Ca)	max. 0.00005	%
cadmium (Cd)	max. 0.01	ppm
cobalt (Co)	max. 0.000001	%
chromium (Cr)	max. 0.000002	%
copper (Cu)	max. 0.02	ppm
iron (Fe)	max. 0.2	ppm
germanium (Ge)	max. 0.000005	%
mercury (Hg)	max. 0.01	ppm
potassium (K)	max. 0.00001	%
lithium (Li)	max. 0.000001	%
magnesium (Mg)	max. 0.00001	%
manganese (Mn)	max. 0.000001	%
molybdenum (Mo)	max. 0.02	ppm
sodium (Na)	max. 0.00005	%
nickel (Ni)	max. 0.000002	%

Hydrochloric acid puriss. p.a., ACS reagent, reagent ISO, reagent Ph. Eur., fuming, 37%, APHA: 10

Parameter	Specification	Units
lead (Pb)	max. 0.02	ppm
strontium (Sr)	max. 0.000001	%
titanium (Ti)	max. 0.00001	%
thallium (Tl)	max. 0.000005	%
vanadium (V)	max. 0.000001	%
zinc (Zn)	max. 0.000005	%
zirconium (Zr)	max. 0.00001	%
heavy metals (ICP) ACS	max. 1	ppm
free chlorine (Cl)	max. 0.5	ppm
bromide (Br)	max. 0.005	%
phosphate (PO ₄)	max. 0.00005	%
sulfate (SO ₄)	max. 1	ppm
sulfite (SO ₃)	max. 1	ppm
appearance of the substance	complying	
APHA	max. 10	
residual solvents	complying	