

# Mini Vortexer

## An Economical Solution Made For Ultimate Function

offers immediate vortex shaking for a variety of tube sizes. A simple, touch start operation enables exceptional mixing performance with one handed operation.

- Made from durable ABS and silicone materials to resist most commonly used chemicals
- Low profile design and small footprint (only 4.3" wide) save valuable space on a bench top and in fume hoods
- Rapid vortex action saves time and enables quick mixing of samples
- Modern design allows easy one handed touch start operation and shaking stops when the tube is lifted
- When performing repetitive procedures, a low activation force helps prevent user fatigue
- Maintenance free design and 3 year warranty helps reduce the cost of ownership
- Stable platform reduces the chance of dropping a sample during operation
- Quiet operation and low vibration helps users stay focused
- Can be used with tubes ranging from 2 mL to 50 mL

### Package includes:

1 Mini Vortexer, 2 Silicone Caps, 1 Low voltage double insulated power adapter with 4 interchangeable plugs



**5**  
Year  
Warranty

### Did you know?

strict standards that include 3<sup>rd</sup> party plant reviews and 100% multi-level product inspections. These actions result in a 99.7% reliability on our equipment and 99.99% reliability on our laboratory supplies.



| Item No. | Color       | L x W x H          | UOM           |
|----------|-------------|--------------------|---------------|
| 120567   | Grey/Purple | 5.1 x 4.3 x 3 in   | 1/ea, 8 ea/cs |
| 120598   | Grey/Blue   | (13 x 11 x 7.5 cm) |               |

#### Specifications

**Speed Range:** 4500 rpm

**Orbit:** 6 mm

**Noise Level:** Full speed, unloaded: 53 dB

**Weight:** 2 lbs (0.9 kg)

Input: 12 VDC, approx. 7.8 W (under load)

**Power:** Adapter Input: 100-240 VAC, 50/60 Hz, 0.3 A  
Adapter Output: 12 VDC, 1A with 4 interchangeable plug adapters. For indoor use, Double Insulated, Level VI efficiency, recognized marks: UL (Canada and U.S.), GS, FCC, CE, and C-Tick



**Warranty:** 5 years

**Certifications:** CE, CB Scheme, and SGS (Canada and U.S.)



EN/IEC 61010-1 ed. 3.1, 2017  
EN/IEC 61010-2-051 ed.3, 2015  
UL Std. 61010-1 ed.3, 2012  
UL Std. 61010-2-051 ed.3, 2015  
CAN/CSA C22.2 No.61010-1-12 (R2017)  
CAN/CSA C22.2 No.61010-2-051 (R2015)  
IEC 61326-1:2013 (IEC 61326-1:2012)  
FCC Part 15, Subpart B: 2015  
ICES-003, Issue 6

U.S. and E.U. Utility Patent Pending; U.S. Design Patent No. D814,045