

Wire Rack Bottle Carrier

Space Saving Design

- 6-Place rack holds bottles up to 80 mm in diameter
- HDPE coated wire for durability and chemical resistance
- Handle design swings down to load and unload without obstruction and swings up for carrying convenience
- For use with flat bottom Centrifuge, General Purpose and Wash Bottles



Item No.	Color	Array	L x W x H in	L x W x H cm	UOM
121005	White <input type="checkbox"/>	2 x 3	10 x 6.9 x 4.1 10.4 H w/ Handle Extended	25.2 x 17.4 x 10.4 26.4 H w/ Handle Extended	1 ea