

Key features

Easy to handle
 Single or dual wavelength
 Long live filter and high UV output
 Ondulex® reflector for optimum UV irradiance
 Lamp stand or holder to add versatility



- Description

The Vilber Lourmat lamps are provided in 254, 312, 365 nm or combined. The unique filter minimizes white light interference allowing you to easily detect weak fluorescence.

The filter has unlimited life expectancy for 312 and 365nm (3000 hours for 254 nm).

- Ordering codes

Code	Tubes (Watt)	nm	$\mu\text{W}/\text{cm}^2$
VL215-L	2x15 W	365	2300
VL215-C	2x15 W	254	1780
VL215-M	2x15 W	312	3000
VL215-LC	2x15 W	365/254	1350/1100
VL215-LM	2x15 W	365/312	1350/1800
VL215-MC	2x15 W	312/254	1800/930
VL115-L	1x15 W	365	1100
VL115-C	1x15 W	254	1000
VL115-M	1x15 W	312	1000
VL6-L	1x6 W	365	800
VL6-C	1x6 W	254	820
VL6-LC	2x6 W	365/254	720/520