



Immersion OIL

**NEW
PACKAGING**



Comfort of use

Transparency

Cleanliness

User safety

DOMINIQUE DEUTSCHER SAS

What makes RAL immersion oil **UNIQUE ?**



COMFORT OF USE

The profiled vial DropStick® has no cap and comes with a built-in dropper.

Thanks to the DropStand® rack you can always have the pair within easy reach.



TRANSPARENCY

Through its high quality, RAL Immersion Oil helps optimize the reading of your slides.

RAL Immersion Oil has an unequalled level of transparency: it has the same refraction index as glass.



CLEANLINESS

The viscosity of the oil has been designed to pour one drop at a time. The concept DropStick® - DropStand® allows an accurate use and no leak on your workbench.

15 ml = up to 650 slides, approximately 650 drops



USER SAFETY

RAL Immersion Oil contains no toxic substances.

RAL IMMERSION PACKS AVAILABLE



DropStand® with DropStick (1 x 15 ml + 1 DropStand) Ref.: 340060-0000

Pack DropStand® Immersion 30 (2 x 15 ml + 1 DropStand) Ref.: 340032-0000

Pack DropStand® Immersion 100 (7 x 15 ml + 1 DropStand) Ref.: 340103-0000

Pack Immersion 150 (6 x 25 ml + 2 built-in dropper) Ref.: 340150-0000

Pack Immersion 300 (6 x 50 ml + 2 built-in dropper) Ref.: 340300-0000

