

## Wall mounted cabinet with blind doors

### Description:

- ✓ Suitable for mounting on the wall or on the service module frame (*with some exceptions*)
- ✓ Cabinets are made of 19mm thickness melamine faced chipboard with ABS edges
- ✓ 2 doors with hinges that can open at 270° angle
- ✓ 1 inside shelf adjustable all over the height every 32mm
- ✓ Steel handles
- ✓ Wall mounting brackets adjustable in 3 dimensions (*screws for mounting to the wall not included*)
- ✓ Color: light grey (similar to RAL 7035)
- ✓ NET weight 34 kg
- ✓ Max load on one shelf 30 kg
- ✓ Max general load 60 kg

### Suitable for :


- ✓ Storage of tools, accessories and labware

### Not suitable for :

- ✓ Storage of acids and alkali
- ✓ Storage of flammable substances

### Dimensions :

- ✓ Length 900mm
- ✓ Depth 370mm
- ✓ Height 730mm



Sample picture

*Available other options and not standard modifications under request*