

Wall mounted cabinet with blind doors

Description:

- ✓ Suitable for mounting on the wall or on the service module frame (*with some exceptions*)
- ✓ Cabinets are made of 19mm thickness melamine faced chipboard with ABS edges
- ✓ 1 door with hinges that can open at 270° angle
- ✓ Steel handles
- ✓ Wall mounting brackets adjustable in 3 dimensions (*screws for mounting to the wall not included*)
- ✓ Color: light grey (similar to RAL 7035)
- ✓ NET weight 12 kg
- ✓ Max general load 60 kg

Suitable for :


- ✓ Storage of tools, accessories and labware

Not suitable for :

- ✓ Storage of acids and alkali
- ✓ Storage of flammable substances

Dimensions :

- ✓ Length 450mm
- ✓ Depth 370mm
- ✓ Height 380mm



Sample picture

Available other options and not standard modifications under request