

## Open wall mounted cabinet

### Description:

- ✓ Suitable for mounting on the wall or on the service module frame (*with some exceptions*)
- ✓ Cabinets are made of 19mm thickness melamine faced chipboard with ABS edges
- ✓ Wall mounting brackets adjustable in 3 dimensions (*screws for mounting to the wall not included*)
- ✓ Color: light grey (similar to RAL 7035)
- ✓ NET weight 11 kg
- ✓ Max general load 60 kg

### Suitable for :

- ✓ Storage of tools, accessories and labware


### Not suitable for :

- ✓ Storage of acids and alkali
- ✓ Storage of flammable substances

### Dimensions :

- ✓ Length 600mm
- ✓ Depth 350mm
- ✓ Height 380mm

*Available other options and not standard modifications under request*



Sample picture