


## 1.3 Tall cabinets



Overview of tall cabinets






- 1 Open
- 2 Hinged door
- 3 Sliding glass door
- 4 Display cabinet
- 5 Pull-out larder style cabinet

Tall cabinets provide large storage space. They can be equipped with a choice of doors with or without a lock.

## 1.3 Tall cabinets

Construction		
<b>Material</b>	High-grade steel (1.0330), electrogalvanised and polyurethane coated	
<b>Colour</b>	Arctic White (NCS S 0505 R80B), similar to RAL Design 260 90 05	
<b>Plinth colour</b>	Anthracite (NCS S 8500N), similar to RAL Design 2000	
<b>Carcass</b>	Module height	External: 1920 mm Internal: 1760 mm
	Module width	External: 300 mm, 600 mm, 900 mm, 1200 mm Internal: less 40 mm
	Depth	Carcass depth: 350 / 500 mm
		External depth: 350 / 500 mm, if open or sliding glass doors External depth: 366 / 516 mm, if doors
Load capacity	Net load: 180 kg	
<b>Doors</b>	Soundproofed, double skin Clip-on hinges, opening angle 270° LSG sliding glass doors	
<b>D handle</b>	Die-cast zinc, matt chrome plated, with label holder	
<b>Lock</b>	Locking system with interchangeable cylinder	
<b>Pull-out trays</b>	Internal pull-out trays or baskets Carriage guides for pull-out tray or baskets	
	Wardrobe pull-out hanging rail	Pull-out length: 350 mm Load capacity: 10 kg
	Internal trays	Pull-out length: 430 mm Load capacity 40 kg or 70 kg
	Pull-out doors	Pull-out length: 470 mm Load capacity 100 kg per tray
	Carriage guides for larder style unit	Pull-out cabinet height: 1920 mm Pull-out cabinet width: 300 mm Load capacity 70 kg net load
<b>Inserts</b>	Suspended basket for larder style unit	250 x 110 x 467 mm
	With plastic shelf	238 x 450 x 12 mm
	Tray insert for larder style unit	250 x 65 x 462 mm
<b>Shelves</b>	Max. 4 removable shelves across the entire width of the cabinet Load capacity: 30 kg	
<b>Plinth</b>	Plinth can be trimmed for skirting	

## 1.3 Tall cabinets

Tall cabinets, depth 500 / 516 mm, height 1920 mm					
	Order no.	Front	Width [mm]	Removable shelves or internal drawers	Additional information
	301-00047	Open	600	3 shelves	
	301-00020			4 shelves	
	301-00018			4 drawers	
	301-00079		900	3 shelves	
	301-00080			4 shelves	
	301-00078			4 drawers	
	301-00019		1200	3 shelves	
	301-00020			4 shelves	
	301-00018			4 drawers	
	301-00054	1 door left	600	3 shelves	Lockable
	301-00056			4 shelves	
	301-00050			4 inner drawers	
	301-00062	1 door right		3 shelves	
	301-00064			4 shelves	
	301-00058			4 Inner drawers	
	301-00084	2 doors	900	3 shelves	Lockable
	301-00086			4 shelves	
	301-00082			4 Inner drawers	
	301-00028		1200	3 shelves	
	301-00030			4 shelves	
	301-00026			4 Inner drawers	
	301-00076	2 sliding glass doors	900	3 shelves	Lockable
	301-00077			4 shelves	
	301-00016		1200	3 shelves	
	301-00017			4 shelves	
	301-00098	2 sliding glass doors above 2 doors below	900	3 shelves	Display cabinet, lockable
	301-00096		1200		