

TECHNICAL SPECIFICATIONS

Trade name	UV range cuvette semi-micro
Use	UV grade with optical windows for optimum transmittance through spectrum range from 280 to 800 nm.
Material	UV grade PMMA

DIMENSIONAL SPECIFICATIONS

Height	mm. 44,90
Base	mm. 12,40 x 12,45
Path length	mm. 10,00
Window	4x22
General dimensional tolerance	mm. +/- 0,10
Capacity	ml. 2,50

GENERAL FEATURES

CE mark	Yes
Autoclavability	No
Sterilization	To be effected by radiations
Food contact suitable	Yes

CHEMICAL RESISTANCE

Categories of substances	Reference	Concen. %	T. 20°	T. 40°	T.° 60
Inorganic acid	Sulphuric acid	98	C	-	-
Organic acid	Benzoic acid	100	B	C	-
Alcohol	Ethanol	100	B	C	-
Aldehydes	Acetaldehyde	100	B	C	-
Inorganic alkali	Sodium hydroxide	50	C	-	-
Organic alkali	Aniline	100	B	C	-
Ketone	Acetone	100	C	C	C
Esther	Ethyl acetate	100	C	-	-
Hydrocarbons, halogenated	Dichloroethylene	100	C	-	-
Hydrocarbons, aromatic	Benzene	100	C	-	-
Hydrocarbons, linear	Hexane	100	C	-	-
Supersolvent	Tetrahydrofuran	100	C	-	-

Legenda (not applicable if neglected):

- **A: fair resistance;** exposure (30 days) to the chemical does not cause any damage.
- **B: sufficient resistance;** exposure causes damage of poor importance, which sometimes is only temporary.
- **C: poor resistance;** exposure to chemical is not allowed, or causes immediate permanent damage.

Results of testing with reference materials are to be considered as indication: in case of specific use it is recommended to carry out preliminary testing..

PACKAGING

Box	Pcs.100
Box	Pcs. 500
Case	Pcs. 1000

Quality Assurance

Massimiliano Capitanio

Technical Direction

Guido Borona

DOMINIQUE DUTSHER SAS