

TECHNICAL SPECIFICATIONS

Trade Name	Stopcock
Use	Ideal for liquids and gasses under low pressure or low vacuum.
Material	Body: high-density polyethylene (PE) Interface: polypropylene (PP)
Other	Operating pressure 0,5 bar

DIMENSIONAL SPECIFICATIONS

Length	mm. 61,00
Diameter	mm. 8,00
Hole Diameter	mm. 10,90
General dimensional tolerance	mm. +/- 0,10

GENERAL FEATURES

CE Mark	No
Autoclavability	No
Sterilization	To be effected by radiations
Food contact suitable	Yes

CHEMICAL RESISTANCE (polyetilène)

Categories of substances	Reference	Concen. %	T. 20°	T. 40°	T.° 60
Inorganic acid	Sulphuric acid	98	B	B	B
Organic acid	Benzoic acid	100	A	A	A
Alcohol	Ethanol	100	A	A	A
Aldehydes	Acetaldehyde	100	A	B	B
Inorganic alkali	Sodium hydroxide	50	A	A	A
Organic alkali	Aniline	100	A	B	C
Ketone	Acetone	100	-	-	-
Esther	Ethyl acetate	100	B	B	B
Hydrocarbons, halogenated	Dichloroethylene	100	B	C	-
Hydrocarbons, aromatic	Benzene	100	B	B	B
Hydrocarbons, linear	Hexane	100	B	B	C
Supersolvent	Tetrahydrofuran	100	B	B	B

Legenda (not applicable if neglected):

- **A: fair resistance;** exposure (30 days) to the chemical does not cause any damage.
- **B: sufficient resistance;** exposure causes damage of poor importance, which sometimes is only temporary.
- **C: poor resistance;** exposure to chemical is not allowed, or cases immediate permanent damage.

Results of testing with reference materials are to be considered as indication: in case of specific use it is recommended to carry out preliminary testing..

PACKAGING

Bag	Pcs. 10
Case	Pcs. 2000

Quality Assurance

Massimiliano Capitanio

Technical Direction

Guido Borona

DOMINIQUE DUTSHER SAS