

TECHNICAL SPECIFICATIONS

Trade name	Blue graduated measuring cylinder, tall form
Use	For liquid conforms to ISO 6706-81 and BS 5404 part. 2 1977
Material	Polymethylpentene TPX (PMP)

DIMENSIONAL SPECIFICATIONS

Height	mm. 139,00
External diameter	mm. 13,50
General dimensional tolerance	mm. +/- 0,2
Graduation	each ml. 2,00
Capacity	ml. 10

GENERAL FEATURES

CE mark	No
Autoclavability	Yes
Sterilization	Gas or chemical
Food contact suitable	Yes

CHEMICAL RESISTANCE

Categories of substances	Reference	Concen. %	T. 20°	T. 40°	T.° 60
Inorganic acid	Sulphuric acid	98	B	B	B
Organic acid	Benzoic acid	100	A	B	B
Alcohol	Ethanol	100	A	B	B
Aldehydes	Acetaldehyde	100	B	C	-
Inorganic alkali	Sodium hydroxide	50	A	A	A
Organic alkali	Aniline	100	B	B	C
Ketone	Acetone	100	B	C	-
Esther	Ethyl acetate	100	A	A	A
Hydrocarbons, halogenated	Dichloroethylene	100	C	-	-
Hydrocarbons, aromatic	Benzene	100	B	C	-
Hydrocarbons, linear	Hexane	100	B	C	-
Supersolvent	Tetrahydrofuran	100	B	B	C

Legenda (not applicable if neglected):

- **A: fair resistance;** exposure (30 days) to the chemical does not cause any damage.
- **B: sufficient resistance;** exposure causes damage of poor importance, which sometimes is only temporary.
- **C: poor resistance;** exposure to chemical is not allowed, or cases immediate permanent damage.

Results of testing with reference materials are to be considered as indication: in case of specific use it is recommended to carry out preliminary testing..

PACKAGING

Box	Pz. 10
Case	Pz. 1600

Quality Assurance

Massimiliano Capitanio

Technical Direction

Guido Borona

DOMINIQUE DUTSHER SAS