

# ROTAX 6.8

## Overhead mixer

The new overhead mixer developed by VELP Scientifica

- Provided with digital display
- More simple, precise, safe
- In accordance with UNI 10802 norm



The overhead mixer ROTAX 6.8 is a VELP solution purposely designed and developed for the evaluation of pollutants solubility in water, from sludges, sediments and solid wastes by wastes treatment plants, wastewater treatment plants, laboratories for wastes analysis, laboratories for environmental analysis (sludges, sediments).

The constant commitment aimed to increase continuously the performances of the equipment has created a NEW VERSION by VELP for this laboratory solution, used with satisfactory results in many laboratories.

The new ROTAX 6.8 is provided with a digital display, an advanced system for speed regulation able to assure a better precision, and with innovative safety devices.

The instrument works in accordance with DIN 38414 standard and UNI 10802 norm.

## Features and Benefits

ROTAX 6.8 is able to hold 6 bottles having 2 litres volume (or, by means of a suitable adapter, 8 bottles having a 1 liter volume).

The instrument can be used when rotating, shaking and mixing is required.

Some benefits of this new unit:

**EASY TO USE** - new digital display, giving the possibility to select and visualize the speed

**PRECISE** - electronic regulation of the speed, from 0 to 30 rpm, 1 rpm selection

**SAFE** – new safety device, to stop the unit if something blocking the rotation occurs

The instrument works in accordance with DIN 38414 and UNI 10802 (“Criteria to admit wastes to dump”).

Technical features	Description
Structure	Metallic, epoxy painted
Number of bottles	6 bottles, 2 liters or 8 bottles, 1 liter, by an adapter
Max height of the 2-liter bottle	280 mm
Min height of the 2-liter bottle	220 mm
Max diameter of the 2-liter bottle	135 mm
Max height of the 1-liter bottle (with adapter)	270 mm
Min height of the 1-liter bottle (with adapter)	200 mm
Max diameter of the 1-liter bottle (with adapter)	110 mm
Display	LCD
Power supply	220 - 240 V / 50 - 60 Hz
Electronic speed control	0 -30 rpm
Speed selection	1 rpm
Power	100 W
Weight	30 Kg (66 lb)
Dimension (W x H x D)	665 x 520 x 470 mm (26.2 x 20.5 x 18.5 in)

Cod. N°	Description
F10600118	Rotax 6.8 overhead mixer
A00001023	Accessory to fit 8 bottles, 1 liter (n° 2 pieces)
A00001021	Bottle, 2 liters, polyethylene
A00001024	Glass bottle, with ground glass cap, 2 liters

Your authorized agent:

We reserve the right to make technical alternations  
We do not assume liability for errors in printing, typing or transmission

