



ES

Overhead Stirrers

Overhead stirrer for low viscosity liquids



Resistant and Easy-to-Use

The ES is an intuitive overhead stirrer ensuring safety with overload, over-current and overheating protection.

- Maximum torque of 15 Ncm
- Supports applications with a maximum viscosity of 1000 mPa*s
- Electronic speed regulation from 50 to 1300 rpm, up to 15 L
- Long life, robust motor
- Easy-chuck to change the shafts without tools
- Automatically stops if blocked – no burn-out or damage
- Overload, overcurrent and overtemperature protection
- Sealed to IP 40 standard



INSTRUMENT - CODE

ES

110-230 V / 50-60 Hz

F201A0152

TECHNICAL DATA

| | |
|---|--|
| CONSTRUCTION MATERIAL | Technopolymer and epoxy painted aluminum alloy |
| CHUCK RANGE | 1 - 10 mm |
| ELECTRONIC PROTECTION RATING CEI EN 60529 | IP 40 |
| ELECTRONIC SPEED REGULATION | From 50 to 1300 rpm |
| STIRRING VOLUME MAX (H ₂ O) | Up to 15 L |
| MAX VISCOSITY | 1000 (mPa*s)* |
| TORQUE MAX | 15 Ncm |
| ALLOWED ROOM TEMPERATURE | From 0 to 40 °C |
| DIMENSION (WXHXD) | 80x160x200 mm (3.1x6.3x7.9 in) |
| POWER | 30 W |
| WEIGHT | 1.3 Kg (2.8 lb) |



We reserve the right to make technical alterations
We do not assume liability for errors in printing, typing or transmission

VELP Official Partner

DESIGNED AND MANUFACTURED IN ITALY



ITALY – HQ
Via Stazione 16
20865 Usmate (MB) Italy
Tel. +39 039 628811
velpitalia@velp.com

INDIA
velpindia@velp.com

USA
155 Keyland Court, Bohemia
NY 11716 - U.S.
Tel. +1 631 573 6002
velpusa@velp.com

CHINA
Xinlong Rd Building 28, Lane 1333
Shanghai city - China
Tel. +86 180 1755 7329
velpchina@velp.com