

**10.200****ELASTICATED PE TRANSPARENT OVERBOOTS****FEATURES & BENEFITS**

- Recommended in food industry and protected environment.
- Fully waterproof & ultra-resistant high-pressure overboots.
- Can be use outside.
- Fully covers the boot.

**TECHNICAL DESCRIPTION**

Product name:	Elasticated PE transparent overboots
Product type:	Single use, non sterile
Composition :	Polyethylene
Confection :	Welded
Thickness :	70 µm
Dimensions :	450 x 390 mm
Weight of a pair:	34 g
Origin :	Asia

**INDUSTRIES**

Pharmaceutical industries / Research laboratories / Nuclear, Electronics, Aeronautical industries / Food industry

**CERTIFICATIONS & STANDARDS**

Manufacturing site : ISO 9001.

**STORAGE CONDITIONS**

Normal conditions of conservation & storage : not to be moisture and sunlight, must be stored in a cool environment or at room temperature.

**LOGISTIC INFORMATIONS**

SPECIFICATIONS OUTER CASE					SPECIFICATIONS CDT
Article	SIZE (mm)	WEIGHT (kg)	Qty / pallet	BARCODE	CDT
10.200	360 x 340 x 350	9,1	30 oc	3 700 381 506 166	10 bags of 50 units