

Air-Displacement Pipette

**PREMIUM PIPETTING COMFORT**



## Pipetting Comfort

PIPETMAN® G offers one of the lowest pipetting forces commercially available. With a redesigned piston assembly system and high quality piston grease, PIPETMAN G guarantees hours of comfortable pipetting.

## Reliable Results

PIPETMAN G relies on the legendary accuracy, precision, and reliability of PIPETMAN with improved pipetting comfort.

## Built-to-Last and Convenient

Made of PVDF and stainless steel, PIPETMAN G offers premium durability. The PIPETMAN G clip ejector allows for convenient access to serviceable parts.



PIPETMAN® G Single Channel				
Model	PIPETMAN® DIAMOND Tips		Part Number	Volume
P2G	D10 DL10	DF10ST DFL10ST	F144054M	0.2-2 µL
P10G	D10 DL10	DF10ST DFL10ST	F144055M	1-10 µL
P20G	D200	DF30ST	F144056M	2-20 µL
P100G	D200	DF100ST	F144057M	10-100 µL
P200G	D200 D300	DF200ST DF300ST	F144058M	20-200 µL
P1000G	D1000 D1200	DF1000ST DF1200ST	F144059M	100-1000 µL
P5000G*	D5000		F144066	500-5000 µL
P10mLG*	D10mL		F144067	1000-10000 µL
PIPETMAN® G Multichannel				
P8x10 P12x10	D10 DL10	DF10ST DFL10ST	F144068 F144069	1-10 µL
P8x20 P12x20	DL10 D200	DFL10ST DF30ST	F144070 F144071	2-20 µL
P8x200 P12x200	D200 D300	DF200ST DF300ST	F144072 F144073	20-200 µL
P8x300 P12x300	D200 D300	DF200ST DF300ST	F144074 F144075	30-300 µL

Models equipped with a tip ejector are only sold with a stainless steel tip ejector. Plastic tip ejector is available as an accessory. Refer to *PIPETMAN G User's Guide LT801122*.

\*P5000G and P10mLG do not have tip ejectors.

Gilson maximum permissible errors are guaranteed only when PIPETMAN pipettes are used with the recommended PIPETMAN DIAMOND Tips.



PIPETMAN G specifications are downloadable from [www.gilson.com](http://www.gilson.com)

[www.gilson.com/contactus](http://www.gilson.com/contactus)

ISO 9001  
CERTIFIED

LT800591/B | ©2019 Gilson S.A.S.  
All rights reserved. All trademarks  
are the property of Gilson, Inc.  
and its subsidiaries.

 **GILSON®**