

Air-Displacement Pipette

PREMIUM PIPETTING COMFORT



Pipetting Comfort

PIPETMAN[®] G offers one of the lowest pipetting forces commercially available. With a redesigned piston assembly system and high quality piston grease, PIPETMAN G guarantees hours of comfortable pipetting.

Reliable Results

PIPETMAN G relies on the legendary accuracy, precision, and reliability of PIPETMAN with improved pipetting comfort.

Built-to-Last and Convenient

Made of PVDF and stainless steel, PIPETMAN G offers premium durability. The PIPETMAN G clip ejector allows for convenient access to serviceable parts.



PIPETMAN® G Single Channel

| Model | PIPETMAN® DIAMOND Tips | | Part Number | Volume |
|---------------------------------|------------------------|----------------------|----------------------------------|---------------|
| P2G | D10 DL10 | DF10ST DFL10ST | F144054M | 0.2-2 µL |
| P10G | D10 DL10 | DF10ST DFL10ST | F144055M | 1-10 µL |
| P20G | D200 | DF30ST | F144056M | 2-20 µL |
| P100G | D200 | DF100ST | F144057M | 10-100 µL |
| P200G | D200 D300 | DF200ST DF300ST | F144058M | 20-200 µL |
| P1000G | D1000 D1200 | DF1000ST DF1200ST | F144059M | 100-1000 µL |
| P5000G* | D5000 | | F144066 | 500-5000 µL |
| P10mLG* | D10mL | | F144067 | 1000-10000 µL |
| PIPETMAN® G Multichannel | | | | |
| P8x10 P12x10 | D10 DL10 | DF10ST DFL10ST | F144068 F144069 | 1-10 µL |
| P8x20 P12x20 | DL10 D200 | DFL10ST DF30ST | F144070 F144071 | 2-20 µL |
| P8x200 P12x200 | D200 D300 | DF200ST DF300ST | F144072 F144073 | 20-200 µL |
| P8x300 P12x300 | D200 D300 | DF200ST DF300ST | F144074 F144075 | 30-300 µL |

Models equipped with a tip ejector are only sold with a stainless steel tip ejector. Plastic tip ejector is available as an accessory. Refer to *PIPETMAN G User's Guide LT801122*.

*P5000G and P10mLG do not have tip ejectors.

Gilson maximum permissible errors are guaranteed only when PIPETMAN pipettes are used with the recommended PIPETMAN DIAMOND Tips.



PIPETMAN G specifications are downloadable from www.gilson.com

www.gilson.com/contactus

ISO 9001
CERTIFIED

LT800591/B | ©2019 Gilson S.A.S.
All rights reserved. All trademarks
are the property of Gilson, Inc.
and its subsidiaries.

GILSON®