



AmpliPur Expert Tips

| | |
|-------------|---------|
| Part Number | F174201 |
|-------------|---------|

Specification

| | |
|---------------------------------------|---|
| Description | AmpliPur Expert Tips, 1-20 µL, graduated, filter tips |
| Dimensions | <ul style="list-style-type: none">Tip length: 52 mmInner diameter tip point: 0.5 mmOutside tip collar diameter: 7 mmRack box dimensions : 122.5 x 90.5 x 77 mm |
| Volume Range | 1-20 µL |
| Nominal Volume of Compatible Pipettes | 20 µL |
| Material (Plastic) | <ul style="list-style-type: none">Tips: Polypropylene (PP)Filter: Polyethylene (PE)Rack: Polypropylene (PP)Heat shrink: Plastic Optical Fibre (POF) |
| Disposable | <ul style="list-style-type: none">Tips: yesRack: reusable |
| Tip Color | Translucent |
| Sterilization | N/A |
| Quality Control | Material control Product inspection: control of characteristics according Gilson's specifications |

Characteristics

| | |
|----------------------------|--|
| Characteristic | The optimized geometry and material (virgin polypropylene) ensures full recovery of the aspirated liquid for consistent results |
| Temperature | Maximum temperature 140°C |
| Autoclavability | Not applicable on filter tip |
| Expiration Date/Shelf Life | 3 years |
| Traceability/Quality | <ul style="list-style-type: none">Complete traceability from production to the userCertificate of conformityQuality statement with protocols and detection thresholds for each batch |
| Other Information | <ul style="list-style-type: none">Compliant to ISO 8655-2 maximum permissible errorsFree of RNase and DNaseCompliant to the use of hazardous substances directive 2015/863/EUGraduation mark at 10 µL |

Packaging Description

| | |
|-------------------------------|---|
| Part Number (Commercial Unit) | F174201 |
| Tip qty/Rack | Rack of 96 tips |
| Tip qty/Commercial Unit (CU) | 10 racks of 96 tips (960 tips) |
| Tip qty/Outer Package | 5 CU of 960 tips (4800 tips) |
| Codification Lot # | YYMMDD - xxxx (DD: Year, MM: Month, DD: Day, - , xxxx: Mould No.) |
| Color Code Rack | Yellow rack |