

Bransonic® M and MH Ultrasonic Baths

General Description

Bransonic M and MH Series cleaners are known for offering a level of precision and reliability you have come to expect from Branson.

- M Series includes 60-minute mechanical timer and continuous operation.
- MH Series includes 60-minute mechanical timer and continuous operation with heating capability.

M and MH Series cleaners offer the following features:

- Sweep frequency eliminates standing waves and creates consistent cavitation throughout the tank.
- 40 kHz rugged industrial transducers.
- Controls are located above and behind the cleaning tank in an easily accessible control tower panel, and raised above the tank to avoid damage from cleaning solutions.
- Convenient built-in pour drains are featured on .5- and .75-gallon models. Tank drains with valves are incorporated on models 1.5-gallon and larger.
- Plastic body, chemical-resistant.

Consult with your Branson representative about the Bransonic accessories and solution best suited for your application needs. **Visit us at www.Bransonic.com**



BRANSON

M Series (Mechanical timer)

Ordering Part No.	Voltage	Model 1800	Model 2800	Model 3800	Model 5800	Model 8800
	120 V	M1800	M2800	M3800	M5800	M8800
Part No.		CPX-952-116R	CPX-952-216R	CPX-952-316R	CPX-952-516R	CPX-952-816R
	230/240 V	M1800-E	M2800-E	M3800-E	M5800-E	M8800-E
Part No.		CPX-952-136R	CPX-952-236R	CPX-952-336R	CPX-952-536R	CPX-952-836R

MH Series (Mechanical timer with heater)

Ordering Part No.	Voltage	Model 1800	Model 2800	Model 3800	Model 5800	Model 8800
	120 V	M1800H	M2800H	M3800H	M5800H	M8800H
Part No.		CPX-952-117R	CPX-952-217R	CPX-952-317R	CPX-952-517R	CPX-952-817R
	230/240 V	M1800H-E	M2800H-E	M3800H-E	M5800H-E	M8800H-E
Part No.		CPX-952-137R	CPX-952-237R	CPX-952-337R	CPX-952-537R	CPX-952-837R

Specifications

	Model 1800	Model 2800	Model 3800	Model 5800	Model 8800
Tank Capacity					
Liters/Gallons	1.9/0.5	2.8/0.75	5.7/1.5	9.5/2.5	20.8/5.5
Tank Size (L/W/D)					
Inches	6 x 5.5 x 4	9.5 x 5.5 x 4	11.5 x 6 x 6	11.5 x 9.5 x 6	19.5 x 11.5 x 6
mm	150 x 140 x 100	230 x 140 x 100	290 x 150 x 150	290 x 240 x 150	495 x 290 x 150
Overall Size (L/W/D)					
Inches	9.9 x 12 x 11.9	13.3 x 12 x 11.9	15.6 x 12.5 x 14.8	15.6 x 15.8 x 14.9	23.5 x 18.3 x 15.4
mm	251 x 304 x 302	337 x 304 x 302	397 x 317 x 377	397 x 401 x 378	596 x 466 x 391
Weight					
Pounds/Kilograms	7/3.2	9/4.1	12/5.4	14/6.4	26/11.8
Frequency	40 kHz	40 kHz	40 kHz	40 kHz	40 kHz
Drain	No	No	Yes	Yes	Yes

NOTE: Tank cover included. For optimum cleaning results, Branson offers a line of accessories including perforated trays, solid trays, beaker covers and support racks for your application needs.

Americas

Branson Ultrasonics Corp.
41 Eagle Road
Danbury, CT 06810, USA
T: 203-796-0400
F: 203-796-2250
Toll Free: 800-732-9262
www.bransonultrasonics.com

Europe

Branson Ultraschall
Niederlassung der Emerson
Technologies GmbH & Co. OHG
Waldstrasse 53-55
63128 Dietzenbach, Germany
T: +49-6074-497-0
F: +49-6074-497-199
www.branson.eu

Asia

Branson Ultrasonics (Shanghai) Co., Ltd.
758 Rong Le Dong Road
Song Jiang, Shanghai, PRC, 201613
T: 86-21-3781-0588
F: 86-21-5774-5100
www.branson.com.cn

All specifications subject to change without notice. All dimensions are nominal.
All ultrasonic baths meet FCC, CSA, CE & UL rules and regulations.
Standard-two year warranty.



© Branson Ultrasonics Corporation 2012.
The Emerson logo is a trademark and service mark
of Emerson Electric Co.
Printed in the U.S.A.

BCL-0003-12