

15.2 Technical data

Display screen	7" LED backlight
Resolution	800×480 pixels
Touch screen	Capacitive
Brightness	450cd/m ²
Picture format	16:9
CPU	Freescale iMX.53x 800MHz / 1.0GHz
Core	ARM Cortex-A8
Memory	RAM: 512MB DDR3 (Optional 1G) ROM: 4GB NAND FLASH (Optional 8G)
Memory card connections	Micro-SD card and USB stick
LAN	Ethernet 10/100M (RJ45)
Bluetooth	Bluetooth 2.1 Host and Slave
Further interfaces	CertoClav Barcode Scanner Slot
Audio	External Audio Jack loudspeaker in front
Speaker	1W
max. Consumption	9W
Acceptable working temperature	-10 – 65 °C
Acceptable storage temperature	-25 – 8 °C
Power supply	DC 9-36V
Dimensions (LBT)	220 × 132 × 36.5 mm
Weight	740g

15.3 Requirements for transport and storage:

- Ambient temperature: 5~40 °C
- Relative air humidity: ≤80%.
- No corrosive gases in the environment

16 Scope of delivery



After you have opened the packaging, please check the product for transport damage. If you find any damage, please contact your dealer and do not operate the device for safety reasons. Please also check if the full scope of delivery is included.

Description	Quantity
Operating instructions	1
Mobile touch screen	1
Power cable	1
Base for touch screen with four fastening screws	1
Interface box for touch screen	1
RS232 cable	1
Touch Pen	1