

Jeio Tech Ultrasonic Cleaners (UCP Series)

Brand: Jeio Tech

Operating at a cleaning frequency of 40kHz, Jeio Tech's Ultrasonic Cleaners (UCP Series) provide maximum cleaning power and strong reliability.

Perfect for cleaning components in different sizes, their #304 stainless steel tanks are easy-to-clean and sealed with a durable/flame resistant cover. These cleaners also feature a simple digital LED display and temperature controller.

Features:

- Durable/flame resistance ABS material used and cover with #304 stainless steel tanks.
- Over-temperature protection with alarm (except for UCP-02).
- Digital LED display using splash-proof keypads timer (1 to 99 min., max. 4 hours operating), temperature monitor (except for UCP-02).
- High-frequency 40 kHz sound waves provide greater cleaning power and increased reliability.
- Multiple output mode (normal/pulse/sweep) with power selection (low/middle/high), (except for UCP-02).
- Before cleaning, dissolved gas removed by degas function (except for UCP-02).
- Drain valve, basket, cover as standard offer (except for UCP-02).



Specifications:

Model(s)		UCP-02	UCP-10	UCP-20
Product Code(s)		BDH532011K	BDH532012K	BDH532013K
Bath Volume (litres)		2	10	20
Temperature Range (°C)		-	Amb. to 70	
Ultrasonic Power (W)		100	300	500
Dimensions	Bath Interior (w x l, d)	142 x 132, 104mm	295 x 240, 160mm	500 x 290, 160mm
	Exterior (w x l x h)	290 x 210 x 200mm	490 x 368 x 297mm	721 x 451 x 297mm
	Net Weight (kg)	2	11	17
Electrical Requirements (230V, 50/60Hz)		0.6A	1.3A	2.2A

Unit 3, Tower Business Park
 Warpsgrove Lane
 Chalgrove
 Oxfordshire
 OX44 7XZ

Tel: (+44) 01865 400321

Email: enquiries@medlinescientific.com

Website: www.medlinescientific.com