



SPECIFICATION SHEET

P19/HF/PB/SG/AGCART/S7

pH Range:	0 – 14
E O Point (pH 7):	-25 mV to +25 mV
Temp Range (°C):	0 – 60
Response Time (seconds):	< 30 secs 95 % FSD
Combination:	Yes
Reference Type:	Ag/AgCl Cartridge, Solid Gel Filled, Double Junction
Junction Type:	Open Hole
Membrane Shape:	Spear
Immersion Dept:	12-15mm
Resistance @ 25°C:	≤ 300 MΩ
Total Shaft Length:	75mm under the cap
Upper Shaft Diameter:	12mm
Upper Shaft length:	30mm
Lower Shaft Diameter:	Cone 8mm to 6.74mm
Lower Shaft Length:	35mm
Connector:	S7 (various colours available)
Cable Length:	N/A
Body Material:	PVC
Shelf Life:	12 Months
Recommended Storage:	4 Molar KCl/AgCl Solution (551-68)
Cleaning solution:	791-15
Refill Electrolyte:	Non-Refillable