

Miniature Shaker KM 2



Description

The orbital shaker KM 2 has a shaking platform of 200 x 295 mm which can be loaded with 2 kg. The stroke is 20 mm and the shaking speed between 5 and 220 rpm.

Basic Equipment

Basic device incl. basic platform and rubber mat

Loading Capacity

Erlenmeyer flasks 100 ml 9 pieces

Erlenmeyer flasks 500 ml 2 pieces

You will find further loading possibilities [here](#)

Details

Motion:	orbital
Shaking platform:	200 x 295 mm
Max. load:	2 kg
Shaking speed:	5 - 220 rpm, in steps of 5
Stroke:	20 mm
LED display:	0 - 99 h 59 min / continuous
Order No.:	6113 000
Accessory:	Universal tray KM Mini Universal tray KM Clamping strip KM

Technical specifications

Electrical supply:	100 - 240 V, 50 / 60 Hz
Enclosure protection:	IP 21
Heat emission:	approx. 4 W
Ambient temperature:	4°C to 45°C
Relative humidity:	~ 95 % (non-condensing)
Dimensions (w x d x h):	250 x 415 x 145 mm
Weight:	8,1 kg