

Reax 20 - for 8 bottles (1-16 rpm)



Overhead shakers for 8 Bottles / 1 to 16 rpm (picture similar)

- Set and continuously adjust the variable speed on the analog control knob from 1 to 16 rpm – ideal for waste water analysis
- Easy and fast attachments of bottles
- Other vessels with 160 - 270-mm height and max. 136-mm diameter can be used with attachments

Reax 20 - for 8 bottles (1-16 rpm) - Technical Data

Overheat protection	self-resetting
Permissible ambient conditions	5 - 31 °C at 80 % rel. humidity 32 - 40 °C decreasing linearly up to max. 50 % rel. humidity
Weight	28 kg
Protection class DIN EN 60529	IP 21
Timer	-
Rotation speed range	1 - 16 rpm
Power input	280 W
Dimensions (l/w/h)	770 x 520 x 465 mm
Max. Load	30 kg
Operating Mode	-
Rotation speed setting	electronic control
Orbit / Stroke	-
Platform size	-
Accessories included	-
Angle	-
Motion	overhead