

Reax 2



- Picture with optional adapter 1 - not included in scope of delivery
- Accepts load capacities up to 1 kg
- Speed continuously adjustable from 20 to 100 rpm
- Select the optional [adapter 1](#) for mixing up to 20 test tubes at the same time as an accessory or the [complete system with universal adapter](#)

Reax 2 - Technical Data

Overheat protection	self-resetting
Permissible ambient conditions	5 - 31 °C at 80 % rel. humidity 32 - 40 °C decreasing linearly up to max. 50 % rel. humidity
Weight	5.2 kg
Protection class DIN EN 60529	IP 21
Timer	-
Rotation speed range	20 - 100 rpm
Power input	27 W
Dimensions (w/d/h)	510 x 235 x 180 mm
Max. Load	1 kg
Operating Mode	-
Rotation speed setting	analog
Orbit / Stroke	-
Platform size	-
Accessories included	-
Angle	-
Motion	overhead