



➤ Technical data

Plarform shakers Hei-MIX

Standard supply voltage	230-240 V 50/60 Hz oder 115 V/60 Hz)
Device fuses	M 1,25 A (230 V) oder T 2,0 A (115 V)
Protective class (IEC 61140)	1 Ⓢ
Protection class (IEC 60529)	IP30
Sound pressure level (dB(A)) (based on IEC 61010)	< 50
Overheat protection	self-resetting
Speed control	analog
Operation mode	timer / continuous


Modell Hei-MIX	Titramax 100/101	Titramax 1000	Vibramax 100	Vibramax 110	Rotamax 120
Dimensions (wxhxd) (mm)	245x310x125	320x375x125	245x310x125	245x310x146	245x310x125
Load capacity (kg)	2	5	2	2	2
Drive	shaded pole motor			asyn-chronus motor	shaded pole motor
Motion	circular vibration			circular vibration	rotation
Orbit (mm)	1,5 / 3	1,5	3	1,5	20
Rotation speed (rpm)	150 - 1.350			150 - 2.500	20 - 300
Supply power (W)	31			46	33
Weight (kg)	5,5	6,5	5,5	5,0	5,5




Performance range / admissible load

Hei-MIX Titramax 100/101/1000

Hei-MIX Vibramax 100



Hei-MIX Vibramax 110



Hei-MIX Rotamax 120

