

## Promax 1020

P/N: 543-22332-00



### The incubating model

- The Promax 1020 is a medium-sized model and accepts load capacities of 5 kg
- Wide range of accessories, attachments and clamps for separatory funnels available
- With a stroke length of 32 mm the Promax model performs an ideal motion for separatory funnels
- Set and continuously adjust the variable speed on the digital display from 30 to 250 rpm
- This model is suitable for the modular incubator system and is recommended for applications which require variable temperature control up to 65 °C
- An digital process timer allows for unattended operation and can be set from 1 to 999 minutes. When the set time has elapsed an acoustic alarm will sound and the operation stops

## Promax 1020 - Technical Data

Overheat protection	self-resetting
Permissible ambient conditions	5 - 31 °C at 80 % rel. humidity 32 - 40 °C decreasing linearly up to max. 50 % rel. humidity
Weight	8 kg
Protection class DIN EN 60529	IP 40
Timer	Yes
Rotation speed range	30 - 250 rpm
Power input	50 W
Dimensions (w/d/h)	320 x 375 x 125 mm
Max. Load	5 kg
Operating Mode	timer or continuous
Rotation speed setting	digital
Orbit / Stroke	32 mm
Platform size	290 x 258 mm
Accessories included	non-skid rubber mat
Angle	-
Motion	reciprocating