

Hei-VAC Vario Control

P/N: 591-00141-00



For Hei-VAP Expert Control / Hei-VAP Ultimate Control

Even if the gas ballast valve is open an excellent ultimate vacuum is reached when working with easily condensable vapors. This makes distilling high boiling point solvents such as DMF or DMSO possible at low bath temperatures.

Condenser is not in scope of delivery.

Rotavac Vario Control - Technical Data

Weight	5.4 kg
Diaphragm pump	Three-stage
Suction capacity	1.7 m ³ /h
Ultimate vacuum	2 mbar
Combinable with a condenser	yes
Power input	160 W
Dimensions without condenser (w/d/h)	167 x 236 x 196 mm

DOMINIQUE DUTSCHER SAS