

FICHE TECHNIQUE

Référence	499712
Désignation	Evaporateur



Description :

- ✓ Lift : Hand lift or Motor lift
- ✓ Rotation speed range : 10 - 280 rpm
- ✓ Rotation speed indicator : 3.5" LCD Display
- ✓ Heating capacity : 1,300 W
- ✓ Overheat protection bath : cut-off at 5 °C over set temperature via separate PT 1000
- ✓ Bath temperature setting : 3.5" LCD Display
- ✓ Heating bath temperature control : electronic / digital
- ✓ Max. size evaporating flask : 5 l
- ✓ Condensing surface : 1,400 cm²
- ✓ Condensing surface XL condenser : 2,200 cm²

Unité de vente :

1 Evaporateur
