

Reax 2

P/N: 541-21001-00



The compact one for small volumes

The Reax 2 with the optional adapter for test tubes is designed for simultaneous mixing of up to 20 vessels with diameters of 10-18 mm. This corresponds to the size of classic test tubes or 15 ml Falcon tubes. Alternatively, you can insert your complete rack into the universal adapter (width: 230 mm, height min./max.: 45 mm/160 mm) of the overhead shaker.

Equipped with a solid metal frame, its design stands for extreme load capacity and reliability. Guaranteed safety during unattended continuous operation.

Reax 2 - Technical Data

Overheat protection	self-resetting
Permissible ambient conditions	5 - 31 °C at 80 % rel. humidity 32 - 40 °C decreasing linearly up to max. 50 % rel. humidity
Weight	5.2 kg
Protection class IEC 60529	IP 21
Timer	-
Rotation speed range	20 - 100 rpm
Power input	27 W
Dimensions (w/d/h)	510 x 180 x 235 mm
Max. Load	1 kg
Operating Mode	-
Rotation speed setting	analog
Orbit / Stroke	-
Platform size	-
Accessories included	-
Angle	-
Motion	overhead