

Hei-VAP Expert - motor lift model with G3 XL vertical glassware



Precise setting of rotation speed and heating bath temperature on the digital touch display or – for quick access during an active process – directly via the knobs on the operating panel.

- Central operating panel with 5" touch display
- Motor lift model with G3 XL vertical glassware - achieve higher evaporation rates due to expanded cooling surface of 2,200 cm²
- Clear display of all values (Basic and Advanced modes)
- With timer, limitation of max. temperature, multilingual menu and text display for error messages
- Separate knobs for rotation and heating with locking function to prevent accidental readjusting
- LED ring lights and pictogram to display the activity even from a distance
- Integrated solvent library to facilitate adjustment of the required vacuum on an external vacuum controller
- USB and Micro SD interfaces
- Optional display of vapor temperature
- Subsequent upgrade to Hei-VAP Expert Control possible, including vacuum and chiller

control

DOMINIQUE DUTSCHER SAS

Hei-VAP Expert - Technical Data

Rotation speed indicator	5" LCD color graphic display
Permissible ambient conditions	5 – 31 °C at 80 % rel. humidity 32 – 40 °C decreasing lineary up to max 50% rel. humidity
Protection class DIN EN 60529	IP 20
Lift	Motor lift
Height adjustment speed	30 mm/s
Height adjustment	155 mm
Drive	brushless DC motor with electronic speed control
Heating capacity	1,300 W
Temp. range heating bath	20 – 210 °C
Temperature accuracy bath	±1K
Overheat protection bath	cut-off at 5 °C over set temperature via separate PT 1000
Bath temperature setting	5" LCD color graphic display
Heating bath temperature control	electronic / digital
Secondary overtemp. cut off	250 °C
Material heating bath	stainless steel AISI 316L
Diameter heating bath	255 mm
Volume heating bath	4.5 l
Display vapor temperature	Yes
Required accessories for display vapor temperature	Vapor temperature sensor
Integrated vacuum controller	-
Timer	Yes
Programmable ramps	Yes
Supply Power	1,400 W
Weight without glassware assembly	16 kg

Dimensions with glassware set G3 (w/d/h)	max. 739 x 407 x 845 mm
Dimensions with glassware set G3 XL (w/d/h)	max. 739 x 407 x 920 mm
Condensing surface	1,400 cm ²
Condensing surface XL condenser	2,200 cm ²
Max. size evaporating flask	5 l
Rotation speed range	10 - 280 rpm
Integrated Hei-CHILL controller	-
Vacuum program DAA mode requires AUTOaccurate-Sensor	-
Solvent library	Yes

DOMINIQUE DUTSCHER SAS