

## Hei-VAP Ultimate - hand lift model with coated G1 diagonal glassware



Precise setting of rotation speed and heating bath temperature on the digital touch display or – for quick access during an active process – directly via the knobs on the operating panel.

- Central operating panel with 7" touch display
- Hand lift model with transparent plastic coated G1 diagonal glassware
- Clear display of all values (Basic and Advanced modes)
- With timer, limitation of max. temperature, multilingual menu and text display for error messages
- Separate knobs for rotation and heating with locking function to prevent accidental readjusting
- LED ring lights and pictogram to display the activity even from a distance
- Integrated solvent library to facilitate adjustment of the required vacuum on an external vacuum controller
- USB and Micro SD plus LAN / RS 232 interfaces (Lab 4.0 ready)
- Optional display of vapor temperature

- Subsequent upgrade to Hei-VAP Ultimate Control possible, including vacuum and chiller control

DOMINIQUE DUTSCHER SAS

## Hei-VAP Ultimate- Technical Data

Rotation speed indicator	7" LCD color graphic display
Permissible ambient conditions	5 – 31 °C at 80 % rel. humidity 32 – 40 °C decreasing lineary up to max 50% rel. humidity
Protection class DIN EN 60529	IP 20
Lift	Hand lift
Height adjustment speed	manual
Height adjustment	155 mm
Drive	brushless DC motor with electronic speed control
Heating capacity	1,300 W
Temp. range heating bath	20 – 210 °C
Temperature accuracy bath	±1K
Overheat protection bath	cut-off at 5 °C over set temperature via separate PT 1000
Bath temperature setting	7" LCD color graphic display
Heating bath temperature control	electronic / digital
Secondary overtemp. cut off	250 °C
Material heating bath	stainless steel AISI 316L
Diameter heating bath	255 mm
Volume heating bath	4.5 l
Display vapor temperature	Yes
Required accessories for display vapor temperature	Vapor temperature sensor
Integrated vacuum controller	-
Timer	Yes
Programmable ramps	Yes
Supply Power	1,400 W
Weight without glassware assembly	16 kg

Dimensions with glassware set G3 (w/d/h)	max. 739 x 477 x 845 mm
Dimensions with glassware set G3 XL (w/d/h)	max. 739 x 477 x 920 mm
Condensing surface	1,400 cm <sup>2</sup>
Condensing surface XL condenser	2,200 cm <sup>2</sup>
Max. size evaporating flask	5 l
Rotation speed range	10 - 280 rpm
Integrated Hei-CHILL controller	-
Vacuum program DAA mode requires AUTOaccurate-Sensor	-
Solvent library	Yes

DOMINIQUE DUTSCHER SAS