



Extremely comfortable and precise dispensing pump Programmable on pump module or via control module

Calibration for exact dispensing
Flexible, thanks to replaceable single and multichannel pump heads

rotarus® volume

rotarus® volume 100		Order No. 950 15 62	
Characteristics		Interfaces	
Flow rate range Depending on the pump head used*	0.0036 - 5400 ml/min		RS232 interfaces
Changeable pump heads	Yes		USB interface
Channels	1 - 12 (Depending on the pump head type used)		Analog input for speed specification
Range of speed	5 - 500 1/min		Analog output for speed
Operation	TFT touchscreen	General data	
External control module	Yes	Housing	White powder coated
Program memory	20	Continuous mode	Yes
Pump direction change	Yes	Motor capacity	85 Watt
Calibration function	Yes	Motor type	DC Motor
Speed control	Load-independent	Max. power consumption	150 VA
Speed configuration TFT touchscreen	TFT touchscreen	Power supply	100-240 VAC ; 50-60 Hz
Speed configuration (increments) 1/min	0.1	Protection class	IP54
Operation modes		Standards	CE
	Pumps according to speed	Depth/width/height in mm	270/100/220
	Pumps according to flow rate	Weight	10.1 kg
	Dispensing according to volume		
	Dispensing according to time		
	Dispensing according to volume in time		
	Cycle dispensing		
	Cycle time specification		
Special functions			
	Tube leakage monitoring		
	Blockage detection		
	Pump head detection		
	Tube detection		
	Stackable		
	Usable on stand		
	Drop-free dispensing		
	System assignment		
	Soft start		
	Tube service life monitoring		
	Configurable via menu		

*Indicated flow rates are approximate values measured with water, at 0 meters suction lift and free outlet.