



Powerful basic model

Precise pumping for small volumes
saves space, thanks to small platform

Programmable on pump module

rotarus® smart

rotarus® smart 30	Order No. 950 11 32
Characteristics	
Flow rate range, depending on the pump head used*	0.0075 – 4250 ml/min
Changeable pump heads	Yes
Channels	1-12 (Depending on the pump head type used)
Range of speed	10 – 350 1/min
Operation	TFT touchscreen
Program memory	No
Pump direction change	Yes
Operation modes	
Pumps according to speed	Yes
Speed control	Load-independent
Speed configuration	TFT touchscreen
Speed configuration (increments)1/min	0.1
Special functions	
Configurable	via menu
Stackable	Yes
Interfaces	
Digital input	Start/Stop ; rotation direction
General data	
Housing	White powder coated
Continuous mode	Yes
Motor capacity	30 Watt
Motor type	DC Motor
Max. Power consumption	100 VA
Power supply	100-240 VAC ; 50-60 Hz
Protection class	IP43
Standards	CE
Depth/width/height in mm	190/83/220
Weight in kg	4,4

*Indicated flow rates are approximate values measured with water, at 0 meters suction lift and free outlet.