

**Bellco Glass, Inc.**  
**Specification Sheet**  
**For Product #: 1965-31000**

**Description: Micro Carrier Impeller Assembly**

**Size: for 1 & 3 L Bellco's Micro Carrier Spinner Flasks**

**Impeller Assembly Specifications:**


Impeller Assembly consists of impeller magnet, magnet holder, paddle & silicone plug.

Impeller magnet: PTFE coated magnet, 76.2mm long x 12.7mm OD (approx.)

Magnet Holder: White PTFE, 177.8mm long x 19.1mm OD

Impeller Paddle: White PTFE, 107.6mm wide x 44.5mm tall x .762mm thick

Silicone Plug: White Silicone material, 11.1mm OD x 7.9mm long (approx.)



**The information contained in this specification sheet we believe is correct to the best of our knowledge. The recommendations and suggestions herein are made without guarantee or representation as to results. We recommend that adequate tests be made in your laboratory or plant to determine if this product meets all of your requirements.**



**BELLCO GLASS, INC.**



Bellco Glass, Inc. · 340 Edrudo Road · Vineland, NJ · 08360

Ver: 7/05