

**Bellco Glass, Inc.**  
**Specification Sheet**  
**For Product #: 1965-50051**

**Description: 50mL Water Jacketed Micro Carrier Spinner Flask Only**

Bellco Spinner Flask is designed for use with a circulating water bath or chiller and magnetic stir plate. Two hose connections accept 3/8" ID silicone tubing to provide temperature regulation. Water Jacketed Spinner Flasks are available complete with MicroCarrier impeller assembly or as components

**Flask Specifications:**

Material: Type 1 Class A Borosilicate Glass

Dimensions: 70mm OD x 120mm Overall Height


Flask Volume: 50mL

Jacket Volume: 40mL approx.

Two 18mm Sidearms angled 45° offset center

One 51mm Screw Thread Center Neck

Supply with: One 51mm rubber lined screw cap, two 18mm Phenolic black rubber lined screw caps



**The information contained in this specification sheet we believe is correct to the best of our knowledge. The recommendations and suggestions herein are made without guarantee or representation as to results. We recommend that adequate tests be made in your laboratory or plant to determine if this product meets all of your requirements.**



**BELLCO GLASS, INC.**



Bellco Glass, Inc. · 340 Edrudo Road · Vineland, NJ · 08360

Ver: 7/05