

Bellco Glass, Inc.
Specification Sheet
For Product #: 1965-50251

Description: 250mL Water Jacketed Spinner Flask Only

Bellco Spinner Flask is designed for use with a circulating water bath or chiller and magnetic stir plate. Two hose connections accept 3/8" ID silicone tubing to provide temperature regulation. Water Jacketed Spinner Flasks are available complete with MicroCarrier impeller assembly or as components

Flask Specifications:

Material: Type 1 Class A Borosilicate Glass

Dimensions: 100mm OD x 150mm Overall Height


Flask Volume: 250mL

Jacket Volume: 175mL approx.

Two 24mm Sidearms angled 55° offset center

One 70mm Screw Thread Center Neck

Supply with: One 70mm blue PP screw cap, two 25mm Phenolic black rubber lined screw caps



The information contained in this specification sheet we believe is correct to the best of our knowledge. The recommendations and suggestions herein are made without guarantee or representation as to results. We recommend that adequate tests be made in your laboratory or plant to determine if this product meets all of your requirements.



BELLCO GLASS, INC.



Bellco Glass, Inc. · 340 Edrudo Road · Vineland, NJ · 08360

Ver: 7/05