

**Bellco Glass, Inc.**  
**Specification Sheet**  
**For Product #: 1965-50501**

**Description: 500mL Water Jacketed Spinner Flask Only**

Bellco Spinner Flask is designed for use with a circulating water bath or chiller and magnetic stir plate. Two hose connections accept 3/8" ID silicone tubing to provide temperature regulation. Water Jacketed Spinner Flasks are available complete with MicroCarrier impeller assembly or as components

**Flask Specifications:**

Material: Type 1 Class A Borosilicate Glass

Dimensions: 140mm OD x 190mm Overall Height


Flask Volume: 500mL

Jacket Volume: 260mL approx.

Two 38mm Sidearms angled 45° offset center

One 70mm Screw Thread Center Neck

Supply with: One 70mm blue PP screw cap, two 38mm Phenolic black rubber lined screw caps



**The information contained in this specification sheet we believe is correct to the best of our knowledge. The recommendations and suggestions herein are made without guarantee or representation as to results. We recommend that adequate tests be made in your laboratory or plant to determine if this product meets all of your requirements.**



BELLCO GLASS, INC.



Bellco Glass, Inc. · 340 Edrudo Road · Vineland, NJ · 08360

Ver: 7/05