

**Bellco Glass, Inc.**  
**Specification Sheet**  
**For Product #: 1965-80100**

**Description: 100mL Bell-Flo™ Spinner Flask**

Bellco Spinner Flask is designed for use with a circulating water bath or chiller and magnetic stir plate. Two hose connections accept 3/8" ID silicone tubing to provide temperature regulation. Water Jacketed Spinner Flasks are available complete with MicroCarrier impeller assembly or as components

**Flask Specifications:**

Material: Type 1 Class A Borosilicate Glass


Dimensions: 63.5mm OD x 135mm Overall Height

Two 32mm Sidearms angled 55° offset center

One 70mm Screw Thread Center Neck

Side Baffles: Three equally spaced baffles, 35mm long x 4mm deep

Supply with: two 32mm PP Blue Screw Caps & PP Blue Pouring Rings



**The information contained in this specification sheet we believe is correct to the best of our knowledge. The recommendations and suggestions herein are made without guarantee or representation as to results. We recommend that adequate tests be made in your laboratory or plant to determine if this product meets all of your requirements.**



BELLCO GLASS, INC.



Bellco Glass, Inc. · 340 Edrudo Road · Vineland, NJ · 08360

Ver: 7/05