

Bellco Glass, Inc.
Specification Sheet
For Product #: 1965-80250

Description: 250mL Bell-Flo™ Spinner Flask

Flask Specifications:

Material: Type 1 Class A Borosilicate Glass

Dimensions: 85mm OD x 140mm Overall Height, 175mm across sidearms


Two 32mm sidearms angled 55° off the centerline

One 70mm Screw Thread Center Neck

Indented Bottom: Prevents dead spot under impeller

Side Baffles: Three equally spaced baffles, 45mm long x 6mm deep

Supply with: Two 32mm PP Blue Screw Caps & PP Blue Pouring Rings



The information contained in this specification sheet we believe is correct to the best of our knowledge. The recommendations and suggestions herein are made without guarantee or representation as to results. We recommend that adequate tests be made in your laboratory or plant to determine if this product meets all of your requirements.



BELLCO GLASS, INC.



Bellco Glass, Inc. · 340 Edrudo Road · Vineland, NJ · 08360

Ver: 7/05



BELLCO GLASS, INC.



Bellco Glass, Inc. · 340 Edrudo Road · Vineland, NJ · 08360

Ver: 7/05