

**Bellco Glass, Inc.**  
**Specification Sheet**  
**For Product #: 1965-80570**

**Description: 500mL Bell-Flo™ Spinner Flask**

**Flask Specifications:**

Material: Type 1 Class A Borosilicate Glass

Dimensions: 110mm OD x 175mm Overall Height, 214mm across sidearms


Two 45mm sidearms angled 45° off the centerline

One 70mm Screw Thread Center Neck

Indented Bottom: Prevents dead spot under impeller

Side Baffles: Three equally spaced baffles, 45mm long x 6mm deep

Supply with: Two 45mm PP Blue Screw Caps & PP Blue Pouring Rings



**The information contained in this specification sheet we believe is correct to the best of our knowledge. The recommendations and suggestions herein are made without guarantee or representation as to results. We recommend that adequate tests be made in your laboratory or plant to determine if this product meets all of your requirements.**



**BELLCO GLASS, INC.**



Bellco Glass, Inc. · 340 Edrudo Road · Vineland, NJ · 08360

Ver: 7/05